

Hex Posts

One End Threaded One End Tapped / Both Ends Threaded, Thread Length & Dia. Configurable

■ One End Threaded One End Tapped

■ Both Ends Threaded, Thread Length & Dia. Configurable

RoHS

Type			Material	Surface Treatment
One End Threaded One End Tapped	Both Ends Threaded	Both Ends Threaded, Thread Length Dia. Configurable		
NLSBH	NLSBL	NLSBP	1018 Carbon Steel	Black Oxide
LSBH	LSBL	LSBP		Electroless Nickel Plating
PLSBH	PLSBL	PLSBP		
SLSBH	SLSBL	SLSBP	304 Stainless Steel	-

• One End Threaded One End Tapped

• Both Ends Threaded

• Both Ends Threaded, Thread Length & Dia. Configurable

• L Tolerance

L	8~300 ±0.2
L	300.5~600 ±0.3
L	600.5~800 ±0.4

⚠ Anti-rust Oil is applied on 1018 Carbon Steel products.

Part Number Type	0.5mm Increment				M / N	(C)	A
	B	L	F	G			
One End Threaded One End Tapped 1018 Carbon Steel NLSBH LSBH PLSBH SLSBH	5	8~50	5~20	5~20	2 2.6	5.8	1.0
	6	15~50	5~30	5~30	3 4	6.9	1.5
	7	20~150	5~30	5~30	3 4	8.1	1.5
	8	20~250	8~40	8~40	4 5	9.2	1.6
	10	25~350	8~42	8~42	4 5 6	11.5	2.0
	12	25~400	10~55	10~55	5 6 8	13.9	2.5
	13	30~400	10~55	10~55	5 6 8	15.0	2.5
	14	35~500	12~60	12~60	6 8 10	16.2	3.0
	17	35~500	12~60	12~60	6 8 10	19.6	3.0
	19	45~500	15~75	15~75	8 10 12	21.9	3.5
	24	55~600	20~80	20~80	10 12 16	27.7	4.0
	27	65~700	25~90	25~90	12 16 20	31.2	5.0
	30	80~800	30~100	30~100	16 20 24	34.6	6.0
	32	80~800	30~100	30~100	16 20 24	36.9	6.0

⚠ L>Nx3+2 only for One End Threaded One End Tapped Type.

Ordering Example	Part Number	L	F	G	M	N
	LSBH10	- 200	- F40	-	M5	N4
	PLSBP10	- 200	- F40	- G35	M5	N4
	SLSBP30	- 750	- F35	- G40	M20	N24

Days to Ship [Configure Online](#)

Alterations	Part Number	L	F	G	M	N	(FC)
	LSBH10	- 200	- F40	-	M5	N4	FC
	SLSBP30	- 750	- F35	- G40	M20	N24	FC

Alterations	Code	Spec.	Price Adder
Undercut	FC	Adds a relief to Dimension A. Ordering Code: FC	

Price [Configure Online](#)

One End Threaded One End Tapped		Unit Price			
Part Number	Type	B	Min. L-200	L200.5-400	L400.5-600
1018 Carbon Steel NLSBH	5		-	-	-
	6		-	-	-
	7		-	-	-
	8		-	-	-
	10		-	-	-
	12		-	-	-
	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-
	5		-	-	-
	6		-	-	-
1018 Carbon Steel Black Oxide LSBH	7		-	-	-
	8		-	-	-
	10		-	-	-
	12		-	-	-
	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-
	5		-	-	-
	6		-	-	-
	7		-	-	-
	8		-	-	-
1018 Carbon Steel Electroless Nickel Plating PLSBH	10		-	-	-
	12		-	-	-
	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-
	5		-	-	-
	6		-	-	-
	7		-	-	-
	8		-	-	-
	10		-	-	-
	12		-	-	-
304 Stainless Steel SLSBH	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-

Both Ends Threaded		Unit Price			
Part Number	Type	B	Min. L-200	L200.5-400	L400.5-600
1018 Carbon Steel NLSBL	5		-	-	-
	6		-	-	-
	7		-	-	-
	8		-	-	-
	10		-	-	-
	12		-	-	-
	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-
	5		-	-	-
	6		-	-	-
1018 Carbon Steel Black Oxide LSBL	7		-	-	-
	8		-	-	-
	10		-	-	-
	12		-	-	-
	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-
	5		-	-	-
	6		-	-	-
	7		-	-	-
	8		-	-	-
1018 Carbon Steel Electroless Nickel Plating PLSBL	10		-	-	-
	12		-	-	-
	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-
	5		-	-	-
	6		-	-	-
	7		-	-	-
	8		-	-	-
	10		-	-	-
	12		-	-	-
304 Stainless Steel SLSBL	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-

Both Ends Threaded, Thread Length Dia. Configurable		Unit Price			
Part Number	Type	B	Min. L-200	L200.5-400	L400.5-600
1018 Carbon Steel NLSBP	5		-	-	-
	6		-	-	-
	7		-	-	-
	8		-	-	-
	10		-	-	-
	12		-	-	-
	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-
	5		-	-	-
	6		-	-	-
1018 Carbon Steel Black Oxide LSBP	7		-	-	-
	8		-	-	-
	10		-	-	-
	12		-	-	-
	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-
	5		-	-	-
	6		-	-	-
	7		-	-	-
	8		-	-	-
1018 Carbon Steel Electroless Nickel Plating PLSBP	10		-	-	-
	12		-	-	-
	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-
	5		-	-	-
	6		-	-	-
	7		-	-	-
	8		-	-	-
	10		-	-	-
	12		-	-	-
304 Stainless Steel SLSBP	13		-	-	-
	14		-	-	-
	17		-	-	-
	19		-	-	-
	24		-	-	-
	27		-	-	-
	30		-	-	-
	32		-	-	-

