

STROKE END BLOCKS

RoHS

① CEB (End block)

PD: Outside diameter of post
M SS400
A 2 bolts

RoHS

② CSB (Stock block)

M SS400

PD	D	D ₁	D ₂	S	h	r ₁	r ₂	r ₃	A	Bolt	ℓ
25	46	31.5	36	37	2	15.75	18	23	22	M4×P0.7	10
32	56	41	45	45	2	20.5	22.5	28	27	M4×P0.7	10
38	72	49	56	60	3	24.5	28	36	35	M5×P0.8	10
50	86	62	68	72	3	31	34	43	42	M6×P1.0	10
60	112	76	84	92	3	38	42	56	55	M8×P1.25	12
80	140	100	108	116	3	50	54	70	69	M8×P1.25	12

■ End blocks

Catalog No.	H ₁	Color	Base unit price
Type	PD	5mm increments	1 ~ 9 pieces
① CEB	25	10 ~ 50	Quotation
	32	10 ~ 50	
		55 ~ 60	
	38	15 ~ 50	
		55 ~ 70	
	50	20 ~ 50	
		55 ~ 80	
60	20 ~ 50		
	55 ~ 80		
80	20 ~ 50		
	55 ~ 80		

■ Stock blocks

Catalog No.	H ₂	Color	Base unit price
Type	PD	5mm increments	1 ~ 9 pieces
② CSB	25	10 ~ 20	Quotation
		25 ~ 40	
	32	10 ~ 20	
		25 ~ 40	
	38	10 ~ 20	
		25 ~ 50	
	50	10 ~ 20	
		25 ~ 50	
	60	10 ~ 20	
		25 ~ 50	
	80	10 ~ 20	
		25 ~ 50	

Order **Catalog No.** - **H₁** - **Color (R·Y)**
CEB 32 - 35 - R

Days to Ship **Quotation**

Price **Quotation**

Catalog No.	① CEB (End block)		② CSB (Stock block)		Base unit price 1~9 sets		
Type	PD	H ₁ 5mm increments	Color	H ₂ 5mm increments	Color	EBW	EBS
EBS (①CEB+②CSB 1 piece) Set product	25	10 ~ 50	R (Red) Y (Yellow)	10 ~ 20	R (Red) Y (Yellow)		
		25 ~ 40		25 ~ 40			
	32	10 ~ 50		10 ~ 20			
		55 ~ 60		25 ~ 40			
	38	15 ~ 50		10 ~ 20			
		55 ~ 70		25 ~ 50			
50	20 ~ 50	10 ~ 20					
	55 ~ 80	25 ~ 50					
60	20 ~ 50	10 ~ 20					
	55 ~ 80	25 ~ 50					
80	20 ~ 50	10 ~ 20					
	55 ~ 80	25 ~ 50					

The guide post sets must be machined so that the blocks can be attached. P.944

Order **Catalog No.** - ① - ②
Type PD H₁ Color (R·Y) H₂ Color (R·Y)
EBS 38 - 40 R - 40 - Y

Days to Ship **Quotation**

Price **Quotation**

Alterations **Catalog No.** - ① - ② - (S·RS·HC)
EBW 38 - 40R - 40-Y - S-HC38
CSB 50 - 35-Y - RS

Alteration	Machining for chain attachment	Machining for reinforced chain (RSC) attachment	H ₁ dimension change
Code	S	RS	HC
Spec.			
1Code	EBW	EBS	EBW
			CSB·EBS
			CEB·EBS·EBW

For chain RSC of alteration RS, P.970.