

DIN Rails

C-Shaped Sensor Rails / Simple Brackets / Grounding Blocks

Feature: DIN Rails for mounting amplifiers for fiber sensor or control panels.

RoHS

Material	Surface Treatment	Part Number		
		Installation Surface 27mm For M4	Installation Surface 31mm For M4	Installation Surface 31mm For M5
6063-T5 Aluminum Alloy	Clear Anodize	DNR274	DNR314	DNR315

No anodizing on the ends and inner surface.
Burr remains inside of the mounting holes.

DNR274 Dimensions: 10, 25, 15, 35, 7.3, 35±0.3, 24, 27, 4.5, 1, L

DNR314 Dimensions: 10, 25, 15, 35, 7.5, 35±0.3, 25, 31, 4.5, 1, L

DNR315 Dimensions: 8, 4, 12.5, 4.5, 7.2, 35±0.3, 25, 31, 1, L

⚠ Rails with L=100, 150 and 200 will be cut at random positions.

Part Number	L	DNR274, 314			DNR315		
		Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate	Unit Price	Volume Discount Rate
DNR274 DNR314 DNR315	100	1~9 pc(s).	10~29 pcs.	1~9 pc(s).	10~49 pcs.		
	150						
	200						
	1000						

⚠ For orders larger than indicated quantity, please request a quotation.

Ordering Example: Part Number - L
DNR274 - 150
DNR315 - 1000

Days to Ship: [Configure Online](#)

EX Example

Fiber Sensor Amplifier

DNR274

Suitable to mount an amplifier for optical fiber sensor.

C-Shaped Sensor Rails **SERCC**

Material: 6063 Aluminum Alloy Surface Treatment: Clear Anodize (except ends)

RoHS

Part Number	L	Unit Price	Volume Discount Rate
SERCC	200		10~
	300		
	500		

Ordering Example: Part Number - L
SERCC - 200

Days to Ship: [Configure Online](#)

Simple Brackets **EYST**

Material: Low Carbon Steel Surface Treatment: Trivalent Chromate

RoHS

Part Number	Number of Mounting Holes	Unit Price
EYST	15	
EYSTE	7	

Ordering Example: Part Number
EYST

Days to Ship: [Configure Online](#)

Price: [Configure Online](#)

EX Example

Bendable at desired positions.

Grounding Blocks **ETB3**

Material: C36000 BrassE-F Surface Treatment: Electroless Nickel Plating

RoHS

Part Number	M	d	Unit Price		
			ETB3	ETB6	ETB12
ETB3	4	4.5			
ETB6	5	5.5			
ETB12	6	6.6			

Ordering Example: Part Number - M
ETB3 - 4

Days to Ship: [Configure Online](#)

Price: [Configure Online](#)

EX Example