



Adjusting Bolts

Adjusting Bolt RoHS



Thread	Type	Material	Surface Treatment
Coarse Thread	AJST	1045 Carbon Steel or Equiv.	Black Oxide
	AJSTM	1045 Carbon Steel or Equiv.	Electroless Nickel Plating
	AJSTS	304 Stainless Steel	-
Fine Thread	AJSTF	1045 Carbon Steel or Equiv.	Black Oxide
	AJSTMF	1045 Carbon Steel or Equiv.	Electroless Nickel Plating
	AJSTFS	304 Stainless Steel	-



Refer to the price list for applicable M size.


Part Number	Type	M	L 5mm Increment	d	T	MxPitch		B	D	C	E	Unit Price							
						Fine Thread	Coarse Thread					Coarse Thread			Fine Thread				
												AJST	AJSTM	AJSTS	AJSTF	AJSTMF	AJSTFS		
(Coarse)																			
AJST	3	10~45	2.5	7	-	3x0.5	3	4.5	6										
AJSTM	4	10~60	3.5	7	4x0.5	4x0.7	3	5.5	7										
AJSTS	5	10~70	4.5	9	5x0.5	5x0.8	4.6	7.5	10										
	6	15~80	5.5	10	6x0.75	6x1.0		8.5											
(Fine)																			
AJSTF	8	20~100	7.5	12	8x0.75	8x1.25	6	11.5	13										
AJSTMF	10	25~100	9.5	16	10x1.0	10x1.5	7	15.5	17										
AJSTFS	12	25~150	11.5	19	12x1.0	12x1.75		17.5											
	16	25~150	15.5	24	-	16x2.0	8	21.5	24										

Ordering Example: Part Number - L: AJST8 - 25 Days to Ship: [Configure Online](#) Price: [Configure Online](#)


Example The combination of parts as illustrated can be selected over Web. Details about Selection Procedure [P.81](#)

e-Catalog Search Key [Search](#)


* If a search key is inputted in e-Catalog Search BOX, the search result is shown on the right side of the screen, "Modular Assembler" area.



Adjusting Bolt - T Compact RoHS




Thread	Type	Material	Surface Treatment
Coarse Thread	AJSTC	1045 Carbon Steel or Equiv.	Black Oxide
	AJSTCM	1045 Carbon Steel or Equiv.	Electroless Nickel Plating
	AJSTCS	304 Stainless Steel	-
Fine Thread	AJSTCF	1045 Carbon Steel or Equiv.	Black Oxide
	AJSTCMF	1045 Carbon Steel or Equiv.	Electroless Nickel Plating
	AJSTCFS	304 Stainless Steel	-




Applicable block is T Compact, Side Mounting Type [P.1465](#).

Part Number	Type	M	L 5mm Increment	d	T	MxPitch		B	D	C	E	Unit Price							
						Fine Thread	Coarse Thread					Coarse Thread			Fine Thread				
												AJSTC	AJSTCM	AJSTCS	AJSTCF	AJSTCMF	AJSTCFS		
(Coarse)																			
AJSTC	4	10~60	3.5	3	4x0.5	4x0.7	3	5.5	5	7									
AJSTCM	5	10~70	4.5		5x0.5	5x0.8	4.6	7.5	8										
AJSTCS	6	15~80	5.5	5	6x0.75	6x1.0		8.5	10										
(Fine)																			
AJSTCF	8	20~100	7.5		8x0.75	8x1.25	6	11.5	13										
AJSTCMF																			
AJSTCFS																			


Ordering Example: Part Number - L: AJSTC8 - 25 Days to Ship: [Configure Online](#) Price: [Configure Online](#)

Example 

Adjusting Bolt - Hex Socket Type RoHS



Thread	Type	Material	Surface Treatment
Coarse Thread	AJSTR	1045 Carbon Steel	Black Oxide
	AJSTMTR	1045 Carbon Steel	Electroless Nickel Plating
Fine Thread	AJSTR	304 Stainless Steel	-
	AJSTMTR	304 Stainless Steel	-




The outer hex head E and the hex socket E1 are not aligned.


Part Number	Type	M	L 5mm Increment	d	T	MxPitch		B	D	C	E	E1	ℓ	Unit Price		
						Coarse Thread	Fine Thread							Coarse Thread		
														AJSTR	AJSTMTR	AJSTR
AJSTR	4	10~50	3.5	7	4x0.7	3	5.5	5	7	2.5	2.5					
AJSTMTR	5	10~50	4.5	9	5x0.8	4.6	7.5	10	8	3	3					
AJSTR	6	15~50	5.5	10	6x1.0		8.5		10	4	4					
AJSTMTR	8	20~50	7.5	12	8x1.25	6	11.5	15	13	5	5					

Ordering Example: Part Number - L: AJSTR4 - 20 Days to Ship: [Configure Online](#) Price: [Configure Online](#)

Adjusting Bolt - Hex Socket Knurled Knobs RoHS



Thread	Type	Material	Surface Treatment
Coarse Thread	AJKTN	1045 Carbon Steel	Black Oxide
	AJKTNM	1045 Carbon Steel	Electroless Nickel Plating
	AJKTNS	304 Stainless Steel	-
Fine Thread	AJKTNF	1045 Carbon Steel	Black Oxide
	AJKTNMF	1045 Carbon Steel	Electroless Nickel Plating
	AJKTNMF	304 Stainless Steel	-




Refer to the price list for applicable M size.


Part Number	Type	M	L 5mm Increment	d	T	MxPitch		B	D	A	F	E2	ℓ	Unit Price					
						Fine Thread	Coarse Thread							Coarse Thread			Fine Thread		
														AJKTN	AJKTNM	AJKTNS	AJKTNF	AJKTNMF	
(Coarse)																			
AJKTN	3	10~45	2.5	7	-	3x0.5	3	4.5	7	10	5	4							
AJKTNM	4	10~60	3.5	7	4x0.5	4x0.7	3	5.5											
AJKTNS	5	10~70	4.5	9	5x0.5	5x0.8	4.6	7.5											
	6	15~80	5.5	10	6x0.75	6x1.0		8.5	15	15	8	7							
(Fine)																			
AJKTNF	8	20~100	7.5	12	8x0.75	8x1.25	6	11.5											
AJKTNMF	10	25~100	9.5	16	10x1.0	10x1.5	7	15.5											
	12	25~150	11.5	19	12x1.0	12x1.75		17.5	25	20	10	9							
	16	25~150	15.5	24	-	16x2.0	8	21.5											

Ordering Example: Part Number - L: AJKTN10 - 80 Days to Ship: [Configure Online](#) Price: [Configure Online](#)

Adjusting Bolts - Knurled Knobs RoHS



Thread	Type	Material	Surface Treatment
Coarse Thread	AJSTK	1045 Carbon Steel	Black Oxide
	AJCarbon Steel	Steel	Electroless Nickel Plating
	AJSTKS	304 Stainless Steel	-



Part Number	Type	M (Coarse)	L 5mm Increment	d	T	B	D	A	F	Unit Price		
										Coarse Thread		
										AJSTK	AJCarbon Steel	AJSTKS
AJSTK	3	10~20	2.5	7	3	4.5	4	16				
AJCarbon Steel	4	10~30	3.5			5.5						
AJSTK	5	10~40	4.5			7.5						
AJCarbon Steel	6	15~50	5.5			8.5						
AJSTKS	8	20~50	7.5	12	6	11.5						

Ordering Example: Part Number - L: AJSTK4 - 25 Days to Ship: [Configure Online](#)

Price: [Configure Online](#)