


Wheeled Conveyors / Wheeled Conveyor Rails / Connecting Parts


Wheeled Conveyor Rails

RoHS




L Standard

PFSSPH (Standard) PFSUPH (Wide Pitch)
PFSPPH (Narrow Pitch)



Wheel Qty. Configurable

PFSSPHF (Standard) PFSUPHF (Wide Pitch)
PFSPPHF (Narrow Pitch)



Part Number	Material	Surface Treatment
PFSSPH	Edge: Low Carbon Steel Wheel: Polyacetal Shaft: Polyacetal	Non-chrome Hot Dip Galvanizing
PFSPPH	Edge: Low Carbon Steel Wheel: Polypropylene	Non-chrome Hot Dip Galvanizing

L Standard

Part Number	L Nominal Length	Actual Length L (mm)	A	H	E	P	D	Wheel Qty.	Mass (kg)	Allowable Load (per Wheel)	Connecting Parts	Unit Price 1-49 pc(s)	Volume Discount Rate 50-
PFSSPH (Standard)	2000	1992	40	30	6.5	27	25	24	73	2.12	JBS50_		
	2400	2397						88	2.56				
	3000	2991						110	3.20				
PFSPPH (Narrow Pitch)	2000	2000	40.1	31.6	4	20	18	10	99	2.50	JBS50_A		
	2500	2500						124	3.13				
	3000	3000						149	3.75				
PFSUPH (Wide Pitch)	2000	2000	40.1	31.6	4	50	36	25	39	2.36			
	2500	2500						49	2.95				
	3000	3000						59	3.54				



Part Number - L - N
PFSSPH - 2400 - 50



Days to Ship [Configure Online](#)

Wheel Qty. Configurable


Part Number	Number of Wheels N	A	H	E	P	D	Wheel Qty.	Mass (kg/m)	Allowable Load (per Wheel)	Connecting Parts	Unit Price / Wheel 1 pc.	Cutting Charge
PFSSPHF	5-110	40	30	6.5	27	25	13.5	1.1	5kg	JBS50		
PFSPPHF	5-149	40.1	31.6	4	20	18	10	1.25	7kg	JBS50_A		
PFSUPHF	5-59	40.1	31.6	4	50	36	25	1.18	10kg	JBS50_A		

Connecting Parts

RoHS



Part Number	Mass (g)	Unit Price 1-49 pc(s)	Volume Discount Rate 50-99
JBS501 JBS501A	180		
JBS504 JBS504A	146		
JBS505 JBS505A	168		
JBS506 JBS506A	192		
JBS507 JBS507A	184		
JBS508 JBS508A	164		



Part Number	Mass (g)	Unit Price 1-49 pc(s)	Volume Discount Rate 50-99
JBS501 JBS501A	180		
JBS504 JBS504A	146		
JBS505 JBS505A	168		
JBS506 JBS506A	192		
JBS507 JBS507A	184		
JBS508 JBS508A	164		

Wheeled Conveyors

RoHS




L Standard

FFSSPH (Standard) FFSPPH (Narrow Pitch)



Wheel Qty. Configurable

FFSSPHF (Standard) FFSPPHF (Narrow Pitch)



Part Number	Material	Surface Treatment
FFSSPH	Edge: A6N01SS-T5 Aluminum Alloy Wheel: Polyacetal	Clear Anodize
FFSPPH	Edge: Low Carbon Steel Wheel: Polypropylene	Non-chrome Hot Dip Galvanizing

L Standard

Part Number	L Nominal Length	A	H	E	P	D	Wheel Qty.	Mass (kg)	Allowable Load (per Wheel)	Unit Price 1-49 pc(s)	Volume Discount Rate 50-
FFSSPH (Economy Type)	1000	40	32	5	50	35	25	20	1.84	10kg	
	1500							30	2.76		
	3000							60	5.52		
FFSPPH (Narrow Pitch)	1000	40	32	5	15	13	10	67	6.39	7kg	
	1500							100	9.42		
	3000							200	18.6		

Wheel Qty. Configurable

Part Number	Number of Wheels N	Mass (kg/m)	Allowable Load (per Wheel)	Connecting Parts	Unit Price / Wheel 1 pc.	Cutting Charge
FFSSPHF	5-110	1.84	10kg	JBS50		
FFSPPHF	5-110	6.39	7kg	JBS50		



Part Number - L - N
FFSSPH - 3000 - 10




Days to Ship [Configure Online](#)

Skid Conveyor Rails / Connecting Parts / Lifting Table Units

Skid Conveyor Rails

RoHS




L Configurable

Part Number	Color	L 1mm Increment	Mass (kg/m)	Unit Price / m
PFSL	28 (Ivory)	150-3000	0.53	

Connecting Parts for Skid Conveyor Rails

RoHS




Part Number	Mass (g)	Unit Price 1-49 pc(s)	Volume Discount Rate 50-99
JBS511	120		
JBS512	168		
JBS513	158		

For orders larger than indicated quantity, please request a quotation.

Lifting Table Units

RoHS




Part Number	Static Load (kg)	Dynamic Load (kg)	Mass	Unit Price 1-19 pc(s)	Volume Discount Rate 20-99
PFJB802 (Main Body - Standard)	100	80	12.5kg		
PFJB803 (Main Body - Panel Detachable Type)	60	50	10.3kg		
PFJB802H (Handle)	-	-	444g		
PFJB305 (Saddle)	-	-	53g		

For orders larger than indicated quantity, please request a quotation.



Part Number - L - N
PFJB802 - 3000 - 10



Days to Ship [Configure Online](#)