


# HARDENED PLATES FOR CORE

—TOP & BOTTOM 2-FACES GRINDED TYPE—



Part Number	M	H	T Thickness	Finishing of A · B · T	Precision Standard
HPSHW	SKH51	57~63HRC	$T \begin{matrix} +0.05 \\ +0.03 \end{matrix}$	Finishing of T: $\sqrt{1.5}^6$  Cutting marks sometimes remain on the side face (dimensions A and B).	Parallelism between the top and bottom planes : 0.02/100mm or less
HPHEW			When $T \leq 0.8$ $T \begin{matrix} +0.05 \\ +0.02 \end{matrix}$ When $T \geq 1$ $T \begin{matrix} +0.3 \\ +0.1 \end{matrix}$		Parallelism between the top and bottom planes : When $T \leq 1.5$ : 0.2/100mm or less When $T \geq 2.0$ : 0.1/100mm or less
HPSWW			$T \begin{matrix} +0.05 \\ +0.03 \end{matrix}$		Parallelism between the top and bottom planes : 0.1/100mm or less

A	B	T	Part Number		Slide Unit Price					
			Type	No.	1~4	5~9	10~29	30~50		
60	+5 +0.1	50	+5 +0.1	HPSHW (SKH51)	0.8					
					0.9					
					1					
					1.3					
					1.5					
					1.8					
					2					
					2.5					
					3					
					3.5					
4										
4.5										
5										
5.5										
6										
8										
10										

Quotation

A	B	T	Part Number		Slide Unit Price					
			Type	No.	1~4	5~9	10~29	30~50		
80	+5 +0.1	70	+5 +0.1	HPHEW (SKH51)	0.5					
					0.6					
					0.8					
					1					
					1.5					
					2					
					3					
					4					
					5					
					6					
8										
10										

Quotation

A	B	T	Part Number		Slide Unit Price					
			Type	No.	1~4	5~9	10~29	30~50		
200	+5 +0.1	100	+5 +0.1	HPSWW (SKH51)	1					
					1.5					
					2					
					2.5					
					3					

Quotation

To be quoted on price & lead time above Max. Q'ty.



Part Number  
HPSHW1  
HPSWW2.5



1 Day

Delivery days depend on subsidiary. P.45

